

Varistar CP Mobile Frame

Power Utilities

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

SPECIFICATIONS

Table 1/3						
Catalog Number	Rack Height	Height	Width	Depth	Color	Color Code
20630-193	24 U	1200 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-194	24 U	1200 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-195	24 U	1200 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-196	24 U	1200 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-199	24 U	1200 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-200	24 U	1200 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-201	24 U	1200 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-202	24 U	1200 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-203	29 U	1400 mm	600 mm	600 mm	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Depth	Color	Color Code
20630-204	29 U	1400 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-205	29 U	1400 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-206	29 U	1400 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-207	29 U	1400 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-208	29 U	1400 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-209	29 U	1400 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-210	29 U	1400 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-211	33 U	1600 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-212	33 U	1600 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-213	33 U	1600 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-214	33 U	1600 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-215	33 U	1600 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-216	33 U	1600 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-217	33 U	1600 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-218	33 U	1600 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-219	38 U	1800 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-220	38 U	1800 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-221	38 U	1800 mm	600 mm	900 mm	Black Grey	RAL 7021

20630-193	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-194	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-195	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-196	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-199	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-200	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-201	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-202	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-203	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-204	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-205	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-206	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-207	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-208	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-209	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-210	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-211	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-212	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile
20630-213	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame		Mobile

20630-252	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Mobile
20630-253	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Mobile
20630-254	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Mobile
20630-255	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Mobile
20630-256	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Mobile

Table 3/3

Catalog Number	Works With
20630-193	Varistar CP
20630-194	Varistar CP
20630-195	Varistar CP
20630-196	Varistar CP
20630-199	Varistar CP
20630-200	Varistar CP
20630-201	Varistar CP
20630-202	Varistar CP
20630-203	Varistar CP
20630-204	Varistar CP
20630-205	Varistar CP
20630-206	Varistar CP
20630-207	Varistar CP

Catalog Number	Works With
20630-208	Varistar CP
20630-209	Varistar CP
20630-210	Varistar CP
20630-211	Varistar CP
20630-212	Varistar CP
20630-213	Varistar CP
20630-214	Varistar CP
20630-215	Varistar CP
20630-216	Varistar CP
20630-217	Varistar CP
20630-218	Varistar CP
20630-219	Varistar CP
20630-220	Varistar CP
20630-221	Varistar CP
20630-222	Varistar CP
20630-223	Varistar CP
20630-224	Varistar CP
20630-225	Varistar CP

Catalog Number	Works With
20630-226	Varistar CP
20630-227	Varistar CP
20630-228	Varistar CP
20630-229	Varistar CP
20630-230	Varistar CP
20630-231	Varistar CP
20630-232	Varistar CP
20630-233	Varistar CP
20630-234	Varistar CP
20630-235	Varistar CP
20630-236	Varistar CP
20630-237	Varistar CP
20630-238	Varistar CP
20630-239	Varistar CP
20630-240	Varistar CP
20630-241	Varistar CP
20630-242	Varistar CP
20630-243	Varistar CP

Catalog Number	Works With
20630-244	Varistar CP
20630-245	Varistar CP
20630-246	Varistar CP
20630-247	Varistar CP
20630-248	Varistar CP
20630-249	Varistar CP
20630-250	Varistar CP
20630-251	Varistar CP
20630-252	Varistar CP
20630-253	Varistar CP
20630-254	Varistar CP
20630-255	Varistar CP
20630-256	Varistar CP

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE