

# Gland



nVent RAYCHEM GL-xx are a range of cable glands for use with various size armoured or non-armoured power cables. The glands are available in different sizes and materials and are approved for use in hazardous areas.

## FEATURES

Available in different sizes and materials

Approved for use in hazardous areas

## SPECIFICATIONS

**Area Classification:** Non-Hazardous; Hazardous

Table 1/2

| Catalog Number | Item Name       | Material  | Finish        | IP Rating | Ambient Temperature | Thread Type |
|----------------|-----------------|-----------|---------------|-----------|---------------------|-------------|
| 1244-019083    | GL-55-M25       | Polyamide | Untreated     | IP66      | -55 to 70 °C        | Metric      |
| 1244-019082    | GL-36-M25       | Polyamide | Untreated     | IP66      | -20 to 70 °C        | Metric      |
| 056622-000     | GL-38-M25-METAL | Brass     | Nickel-Plated | IP66      | -60 to 140 °C       | Metric      |
| 1244-017517    | GL-33           | Brass     | Nickel-Plated | IP66      | -60 to 140 °C       | NPT         |
| 1244-017518    | GL-34           | Brass     | Nickel Plated | IP66      | -60 to 140 °C       | NPT         |
| 1244-000847    | GL-45-M32       | Polyamide | Untreated     | IP66      | -55 to 70 °C        | Metric      |

| CatalogNumber | Item Name | Material  | Finish    | IP Rating | Ambient Temperature | Thread Type |
|---------------|-----------|-----------|-----------|-----------|---------------------|-------------|
| 1244-007003   | GL-51-M40 | Polyamide | Untreated | IP66      | -55 to 70 °C        | Metric      |

Table 2/2

| Catalog Number | Item Name       | Thread Size | Locknut Included | For Armored Cable |
|----------------|-----------------|-------------|------------------|-------------------|
| 1244-019083    | GL-55-M25       | M25         | No               | No                |
| 1244-019082    | GL-36-M25       | M25         | No               | No                |
| 056622-000     | GL-38-M25-METAL | M25         | Yes              | Yes               |
| 1244-017517    | GL-33           | 3/4"        | No               | Yes               |
| 1244-017518    | GL-34           | 3/4"        | No               | No                |
| 1244-000847    | GL-45-M32       | M32         | No               | No                |
| 1244-007003    | GL-51-M40       | M40         | No               | No                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**