


MONI-PT100-NH RTD Sensor Assembly for Non-Hazardous Areas



nVent RAYCHEM MONI-PT100-NH sensor is a two-wire platinum resistance temperature detector (RTD), supplied with glass fiber reinforced polycarbonate junction box, for non-hazardous areas.

FEATURES

Simple and fast to install: supplied with glass fiber reinforced polycarbonate junction box and cage clamp terminals

Temperature measuring range: -50 °C to +180 °C

SPECIFICATIONS

Table 1/1

Catalog Number	Item Name	Housing Material	Mounting	Sensor Type	Max Measuring Range	Fixed Cable to Sensor
140910-000	PT100-NH	Polycarbonate	Bracket	PT100	180 °C	Yes

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT