

# CompacPRO Desktop Case, Unshielded



The nVent SCHROFF CompacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frame and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

## CERTIFICATIONS



## FEATURES

Desktop case for individual assembly

Aluminum construction ensures robust solution

International dimensions in accordance with IEC 6297-3-101

Side panel with integrated handle function

Front and rear identical, depth-symmetrical construction

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

## SPECIFICATIONS

|                        |                                           |
|------------------------|-------------------------------------------|
| <b>Product Type:</b>   | Case                                      |
| <b>Type:</b>           | Case for Individual Electronic Components |
| <b>Product Family:</b> | CompacPRO                                 |

Table 1/3

| Catalog Number | Rack Height | Height | Rack Width | Width | Depth | Package Quantity |
|----------------|-------------|--------|------------|-------|-------|------------------|
|----------------|-------------|--------|------------|-------|-------|------------------|

|           |    |         |      |       |       |   |
|-----------|----|---------|------|-------|-------|---|
| 14575-023 | 2U | 102.6mm | 42HP | 257mm | 271mm | 1 |
| 14575-025 | 2U | 102.6mm | 42HP | 257mm | 331mm | 1 |
| 14575-027 | 2U | 102.6mm | 42HP | 257mm | 391mm | 1 |
| 14575-063 | 2U | 102.6mm | 84HP | 471mm | 271mm | 1 |
| 14575-065 | 2U | 102.6mm | 84HP | 471mm | 331mm | 1 |
| 14575-067 | 2U | 102.6mm | 84HP | 471mm | 391mm | 1 |
| 14575-103 | 3U | 147.1mm | 28HP | 186mm | 271mm | 1 |
| 14575-105 | 3U | 147.1mm | 28HP | 186mm | 331mm | 1 |
| 14575-123 | 3U | 147.1mm | 42HP | 257mm | 271mm | 1 |
| 14575-125 | 3U | 147.1mm | 42HP | 257mm | 331mm | 1 |
| 14575-127 | 3U | 147.1mm | 42HP | 257mm | 391mm | 1 |
| 14575-143 | 3U | 147.1mm | 63HP | 364mm | 271mm | 1 |
| 14575-145 | 3U | 147.1mm | 63HP | 364mm | 331mm | 1 |
| 14575-147 | 3U | 147.1mm | 63HP | 364mm | 391mm | 1 |
| 14575-163 | 3U | 147.1mm | 84HP | 471mm | 271mm | 1 |
| 14575-165 | 3U | 147.1mm | 84HP | 471mm | 331mm | 1 |
| 14575-167 | 3U | 147.1mm | 84HP | 471mm | 391mm | 1 |
| 14575-169 | 3U | 147.1mm | 84HP | 471mm | 451mm | 1 |
| 14575-171 | 3U | 147.1mm | 84HP | 471mm | 511mm | 1 |

|           |    |         |      |       |       |   |
|-----------|----|---------|------|-------|-------|---|
| 14575-223 | 4U | 191.6mm | 42HP | 257mm | 271mm | 1 |
| 14575-225 | 4U | 191.6mm | 42HP | 257mm | 331mm | 1 |
| 14575-243 | 4U | 191.6mm | 63HP | 364mm | 271mm | 1 |
| 14575-245 | 4U | 191.6mm | 63HP | 364mm | 331mm | 1 |
| 14575-247 | 4U | 191.6mm | 63HP | 364mm | 391mm | 1 |
| 14575-265 | 4U | 191.6mm | 84HP | 471mm | 331mm | 1 |
| 14575-267 | 4U | 191.6mm | 84HP | 471mm | 391mm | 1 |
| 14575-269 | 4U | 191.6mm | 84HP | 471mm | 451mm | 1 |
| 14575-271 | 4U | 191.6mm | 84HP | 471mm | 511mm | 1 |
| 14575-445 | 6U | 280.5mm | 63HP | 364mm | 331mm | 1 |
| 14575-447 | 6U | 280.5mm | 63HP | 364mm | 391mm | 1 |
| 14575-463 | 6U | 280.5mm | 84HP | 471mm | 271mm | 1 |
| 14575-465 | 6U | 280.5mm | 84HP | 471mm | 331mm | 1 |
| 14575-467 | 6U | 280.5mm | 84HP | 471mm | 391mm | 1 |
| 14575-469 | 6U | 280.5mm | 84HP | 471mm | 451mm | 1 |
| 14575-471 | 6U | 280.5mm | 84HP | 471mm | 511mm | 1 |

Table 2/3

| Catalog Number | Usable Height | Usable Width | Front Frame Construction | Cooling Option | Complies With   | EMC Shielding |
|----------------|---------------|--------------|--------------------------|----------------|-----------------|---------------|
| 14575-023      | 84.4mm        | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |

| CatalogNumber | Usable Height | Usable Width | Front Frame Construction | Cooling Option | Complies With   | EMC Shielding |
|---------------|---------------|--------------|--------------------------|----------------|-----------------|---------------|
| 14575-025     | 84.4mm        | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-027     | 84.4mm        | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-063     | 84.4mm        | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-065     | 84.4mm        | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-067     | 84.4mm        | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-103     | 129.3mm       | 148mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-105     | 129.3mm       | 148mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-123     | 129.3mm       | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-125     | 129.3mm       | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-127     | 129.3mm       | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-143     | 129.3mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-145     | 129.3mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-147     | 129.3mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-163     | 129.3mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-165     | 129.3mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-167     | 129.3mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-169     | 129.3mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-171     | 129.3mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |

| CatalogNumber | Usable Height | Usable Width | Front Frame Construction | Cooling Option | Complies With   | EMC Shielding |
|---------------|---------------|--------------|--------------------------|----------------|-----------------|---------------|
| 14575-223     | 173.8mm       | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-225     | 173.8mm       | 219mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-243     | 173.8mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-245     | 173.8mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-247     | 173.8mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-265     | 173.8mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-267     | 173.8mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-269     | 173.8mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-271     | 173.8mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-445     | 262.9mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-447     | 262.9mm       | 326mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-463     | 262.9mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-465     | 262.9mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-467     | 262.9mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-469     | 262.9mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |
| 14575-471     | 262.9mm       | 432mm        | Single Piece             | No             | IEC 60297-3-103 | No            |

Table 3/3

| Catalog Number | Finish        | Material | Protection Rating | Static Load | Quick Ship |
|----------------|---------------|----------|-------------------|-------------|------------|
| 14575-023      | Powder Coated | Aluminum | IP20              | 30kg        | No         |

| Catalog Number | Finish        | Material | Protection Rating | Static Load | Quick Ship |
|----------------|---------------|----------|-------------------|-------------|------------|
| 14575-025      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-027      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-063      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-065      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-067      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-103      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-105      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-123      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-125      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-127      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-143      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-145      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-147      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-163      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-165      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-167      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-169      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-171      | Powder Coated | Aluminum | IP20              | 30kg        | No         |

| Catalog Number | Finish        | Material | Protection Rating | Static Load | Quick Ship |
|----------------|---------------|----------|-------------------|-------------|------------|
| 14575-223      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-225      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-243      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-245      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-247      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-265      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-267      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-269      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-271      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-445      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-447      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-463      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-465      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-467      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-469      | Powder Coated | Aluminum | IP20              | 30kg        | No         |
| 14575-471      | Powder Coated | Aluminum | IP20              | 30kg        | No         |

## ADDITIONAL PRODUCT DETAILS

---

GND / earthing connections in accordance with

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**