


Insertor/Extractor Handle Type IEL, Grey Lever, Black Button, Bottom, 10 Pieces


CATALOG NUMBER

20817-690



The inserter/extractor handle, type IEL in accordance with IEEE 1101.10. 0,1" offset Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

0.1" offset is used for PSUs with SMD Plus

PRODUCT ATTRIBUTES

Package Quantity: 10

Handle Type: IEL; Bottom Front

Color: Grey

Material: Polycarbonate

Product Type: Handle

Type: Inserter/Extractor, 0.1" Offset

Works With: Front Panels

Please order Coding pegs and Microswitch separately.

Technical drawing of the 3000 Series Locking System, showing three views: front, side, and bottom.

Front View (Top Left): Shows the main body of the lock with dimensions: 2.5, 6.1, 3.6, 35, 2.5, 3.8, 26, 8.55, 8.15, 12.75, 2.5, 22.75, and a hole diameter of $\varnothing 2.95$.

Side View (Top Right): Shows the side profile of the lock with dimensions: 2.5, 6.1, 3.6, 35, 2.5, 3.8, 26, 8.55, 8.15, 12.75, 2.5, and 22.75.

Bottom View (Bottom Left): Shows the bottom profile of the lock with dimensions: 20, 2.54, 2.54, 6.61, 2.54, 7.62, and a hole diameter of $\varnothing 2.95$.

Top View (Bottom Right): Shows the top profile of the lock with dimensions: 20, 2.54, 2.54, 6.61, 2.54, 7.62, and a hole diameter of $\varnothing 2.95$.

Isometric View (Center): Shows the lock assembly with a handle and a bolt. A dimension of 6.61 is indicated for the handle length.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE