

# 108 Two Hole Strap for CPVC Pipe



## **CERTIFICATIONS**





## **FEATURES**

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screws

## **SPECIFICATIONS**

Finish: Pregalvanized


Material: Steel


Table 1/2							
Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	В	С	
1080125EG	1 1/4" Min	1.66"	7/32"	4 1/4"	3 1/4"	1 3/16"	
1080100EG	1"	1.31"	7/32"	3 1/2"	2 1/2"	1 3/16"	
1080150EG	1 1/2"	1.9"	7/32"	4 7/16"	3 7/16"	1 3/16"	

CatalogNumber	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	В	С
1080200EG	2" Min	2 3/8"	7/32"	4 15/16"	3 15/16"	1 3/16"
1080075EG	3/4"	1.05"	7/32"	3 1/4"	2 1/4"	1 3/16"

Table 2/2				
Catalog Number	Hanger Spacing			
1080125EG	6.5' Max			
1080100EG	6' Max			
1080150EG	7' Max			
1080200EG	8' Max			
1080075EG	5.5' Max			

# **DIAGRAMS**





## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

