

300 Universal Beam Clamp



CERTIFICATIONS







FEATURES

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society (MSS) SP-58 (Type 19 and 23)

SPECIFICATIONS

Material: Cast Iron

Table 1/2							
Catalog Number	Finish	Rod Size (RS)	Flange Thickness (FT)	A	Torque (TQ)		
3000037EG	Electrogalvanized	3/8"	3/4" Max	1 1/8"	5 ft·lbf		
3000037PL	Plain	3/8"	3/4" Max	1 1/8"	5 ft·lbf		
3000050EG	Electrogalvanized	1/2"	3/4" Max	1 1/8"	8 ft·lbf		
3000050PL	Plain	1/2"	3/4" Max	1 1/8"	8 ft·lbf		


Catalog Number	Finish	Rod Size (RS)	Flange Thickness (FT)	A	Torque (TQ)
3000062EG	Electrogalvanized	5/8"	3/4" Max	1 1/8"	5 ft·lbf
3000062PL	Plain	5/8"	3/4" Max	1 1/8"	5 ft·lbf
3000075EG	Electrogalvanized	3/4"	3/4" Max	1 1/8"	5 ft·lbf
3000075PL	Plain	3/4"	3/4" Max	1 1/8"	5 ft·lbf
3000087EG	Electrogalvanized	7/8"	3/4" Max	1 1/8"	5 ft·lbf
3000087PL	Plain	7/8"	3/4" Max	1 1/8"	5 ft·lbf


Table 2/2							
Catalog Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications				
3000037EG	500lb	250lb	UL, FM Approved, Pipe Hanger Components, cUL				
3000037PL	500lb	250lb	UL, FM Approved, Pipe Hanger Components, cUL				
3000050EG	950lb	760lb	UL, FM Approved, Pipe Hanger Components, cUL				
3000050PL	950lb	760lb	UL, FM Approved, Pipe Hanger Components, cUL				
3000062EG	950lb	760lb	UL, cUL				
3000062PL	950lb	760lb	UL, cUL				
3000075EG	950lb	760lb	UL, cUL				
3000075PL	950lb	760lb	UL, cUL				
3000087EG	950lb	760lb	UL, cUL				
3000087PL	950lb	760lb	UL, cUL				

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF **TRACHTE**

