

# 327 Malleable Iron Side Beam Attachment



## **FEATURES**

Pre-threaded structural attachment fastened to wall or the side of a joist to support hanger rod where two #43 Wood Drive Screws are necessary for proper support

#### **SPECIFICATIONS**


Material: Steel

Table 1/1						
Catalog Number	Finish	Rod Size (RS)	A	В	Screw Diameter (Sc)	Static Load (F)
3270037EG	Electrogalvaniz ed	3/8"	2 3/8"	15/16"	14"	250lbf
3270037PL	Plain	3/8"	2 3/8"	15/16"	14"	250lbf
3270050PL	Plain	1/2"	2 3/4"	1 5/16"	16"	480lbf
3270050EG	Electrogalvaniz ed	1/2"	2 3/4"	1 5/16"	16"	480lbf

## ADDITIONAL PRODUCT DETAILS

Load rating dependent on wood structure strength.

Follow fastener manufacturer's recommended shear and pull-out strength when fastening to the structure. Fastener not included.



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC** 

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

TRACHTE

