

# **35RS Two Hole Retainer Strap**



## **FEATURES**

Retainer strap for beam clamps

## **SPECIFICATIONS**

Finish: Pregalvanized

Material: Steel

Table 1/1					
Catalog Number	Length (L)	Width (W)	Flange Width	Rod Size 1 (RS1)	Rod Size 2 (RS2)
035RS0800EG	8"	15/16"	6" Max	3/8"	1/2"
035RS1000EG	10"	15/16"	8" Max	3/8"	1/2"
035RS1400EG	14"	15/16"	12" Max	3/8"	1/2"
035RS1200EG	12"	15/16"	10" Max	3/8"	1/2"
035RS1600EG	16"	15/16"	14" Max	3/8"	1/2"
035RS0600EG	6"	15/16"	4" Max	3/8"	1/2"
035RS1800EG	18"	15/16"	16" Max	3/8"	1/2"

#### ADDITIONAL PRODUCT DETAILS

Field bend and use jam nut over hanger rod to secure.

## **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

TRACHTE

