

# **401 Clevis Hanger**



#### **CERTIFICATIONS**







#### **FEATURES**

Recommended for the suspension of stationary non-insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

## **SPECIFICATIONS**

Finish: Electrogalvanized;Pregalvanized

Material: Steel


Table 1/2						
Catalog Number	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	В	С
4010050EG	1/2"	0.84"	3/8"	2 5/16"	1 1/8"	3/8"
4010075EG	3/4"	1.05"	3/8"	2 1/2"	1 1/4"	3/8"

CatalogNumber	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	В	С
4010100EG	1"	1.31"	3/8"	2 13/16"	1 3/8"	3/8"
4010125EG	1 1/4" Min	1.66"	3/8"	3 1/8"	1 9/16"	3/8"
4010150EG	1 1/2"	1.9"	3/8"	3 11/16"	2 1/16"	11/16"
4010200EG	2" Min	2 3/8"	3/8"	4 5/16"	2 1/2"	7/8"
4010250EG	2 1/2"	2 7/8"	1/2"	5 5/16"	3 1/16"	1"
4010300EG	3"	3 1/2"	1/2"	6 1/16"	3 1/2"	1 1/8"
4010350EG	3 1/2"	4"	1/2"	6 13/16"	4"	1 5/16"
4010400EG	4"	4 1/2"	5/8"	7 7/16"	4 3/8"	1 3/8"
4010500EG	5"	5 9/16"	5/8"	9 1/16"	5 1/8"	1 5/8"
4010600EG	6"	6 5/8"	3/4"	10 9/16"	6"	1 7/8"
4010800EG	8"	8 5/8"	3/4"	14"	8"	3 1/8"
4011000EG	10"	10 3/4"	7/8"	16 1/2"	9"	2 9/16"
4011200EG	12"	12 3/4"	7/8"	18 5/8"	10 3/16"	3 1/16"

Table 2/2				
Catalog Number	Static Load (F)	Certifications		
4010050EG	600lbf	UL, cUL, ITB		
4010075EG	600lbf	UL, cUL, ITB		
4010100EG	600lbf	UL, cUL, ITB		
4010125EG	600lbf	UL, cUL, ITB		

Catalog Number	Static Load (F)	Certifications
4010150EG	600lbf	UL, cUL, ITB
4010200EG	600lbf	UL, cUL, ITB
4010250EG	1130lbf	UL, cUL, ITB
4010300EG	1130lbf	UL, cUL, ITB
4010350EG	1130lbf	UL, cUL
4010400EG	1130lbf	UL, cUL, ITB
4010500EG	1430lbf	UL, cUL, ITB
4010600EG	1940lbf	UL, cUL, ITB
4010800EG	2000lbf	UL, cUL, ITB
4011000EG	3600lbf	ITB
4011200EG	3800lbf	ITB

## **DIAGRAMS**





## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.