

510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

CERTIFICATIONS



FEATURES

Only one tool needed to tighten due to serrated wash-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load (F)
5100050EG	1/2"	0.84"	7/16"	8 1/2"	1"	255lb
5100075EG	3/4"	1.05"	7/16"	9"	1"	255lb
5100100EG	1"	1.31"	7/16"	9"	1"	255lb

CatalogNumber	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load (F)
5100125EG	1 1/4" Min	1.66"	7/16"	9 7/16"	1"	255lb
5100150EG	1 1/2"	1.9"	7/16"	9 7/8"	1"	255lb
5100200EG	2" Min	2 3/8"	7/16"	10 1/4"	1 3/16"	255lb
5100250EG	2 1/2"	2 7/8"	7/16"	11"	1 3/16"	390lb
5100300EG	3"	3 1/2"	7/16"	11 3/4"	1 3/16"	530lb
5100400EG	4"	4 1/2"	9/16"	13"	1 1/2"	810lb
5100500EG	5"	5 9/16"	9/16"	14 1/2"	1 1/2"	1160lb
5100600EG	6"	6 5/8"	9/16"	16"	2"	1570lb
5100800EG	8"	8 5/8"	11/16"	18 1/4"	2"	2500lb
5101000EG	10"	10 3/4"	11/16"	20 5/8"	2"	2500lb
5101200EG	12"	12 3/4"	11/16"	22 3/8"	2"	2700lb
5101400EG	14"	14"	11/16"	24 1/8"	2"	2700lb
5101600EG	16"	16"	13/16"	27 7/8"	2 1/2"	2900lb

Table 2/2

Catalog Number	Certifications
5100050EG	
5100075EG	
5100100EG	
5100125EG	



Catalog Number	Certifications
5100150EG	
5100200EG	cUL, ITB, UL
5100250EG	cUL, UL, ITB
5100300EG	UL, cUL, ITB
5100400EG	ITB, cUL, UL
5100500EG	UL, cUL
5100600EG	UL, cUL
5100800EG	UL, cUL
5101000EG	
5101200EG	
5101400EG	
5101600EG	

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

