

510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

CERTIFICATIONS





FEATURES

Only one tool needed to tighten due to serrated wash-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2							
Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	В	Static Load (F)	
5101200EG	12"	12 3/4"	11/16"	22 3/8"	2"	2700lb	
5100800EG	8"	8 5/8"	11/16"	18 1/4"	2"	2500lb	
5101000EG	10"	10 3/4"	11/16"	20 5/8"	2"	2500lb	


Table 2/2				
Catalog Number	Certifications			
5101200EG				
5100800EG	UL, cUL			
5101000EG				


ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:





Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF **TRACHTE**



©2025 nVent, All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.