

520 nVent CADDY EZ Riser, Epoxy Coated



FEATURES

Recommended for suspending vertical steel pipe risers where it is undesirable to have the steel of the hanger in direct contact with the pipe

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

Slotted holes make assembly easy, eliminating loose hardware

Bolts are accessible from the front, serrated washer head design means no wrench required on back side for tightening

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A
5200250EP	Steel	Epoxy Powder Coated, Electrogalvanized	2 1/2"	2 7/8"	7/16"	11"

Table 2/2

Catalog Number	B	Screw Diameter (Sc)	Screw Length (L)	Static Load (F)
5200250EP	1 3/16"	3/8"	1 1/2"	390lbf

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

