

# **Adjustable Mud Ring**



## **CERTIFICATIONS**





### **FEATURES**

Adjustable mud ring accommodates various thicknesses of drywall

Can be adjusted after the installation of drywall

## **SPECIFICATIONS**

Finish: Pregalvanized

Material: Steel

Table 1/1				
Catalog Number	Gang	Box Size	Drywall Thickness	
AMR1020SG	1	4"	1/2" - 1 1/4"	
AMR1024DG41	2	4 11/16"	1/2" - 1 1/2"	
AMR1024DG	2	4"	1/2" - 1 1/2"	

Catalog Number	Gang	Box Size	Drywall Thickness
AMR1224TG	3		5/8" - 1 1/2"
AMR1224SG	1	4"	5/8" - 1 1/2"
AMR1224SG41	1	4 11/16"	5/8" - 1 1/2"

#### ADDITIONAL PRODUCT DETAILS

Can be used with nVent CADDY Adjustable Mud Ring, Extension (sold separately) that is attached to inner ring for additional depths up to 2¼ in

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO

**SCHROFF** 

**TRACHTE** 



nVent.com/CADDY 2

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.