


B18-CO-EM Box/Multiple Conduit Hanger with Flange Clip



FEATURES

One assembly provides support for electrical box and/or conduit from beam flanges

Comes with one conduit clip attached to each side with the ability to attach up to two more per side

Eliminates need for offset bending conduit

66% less Drop Wires (rod/wire application)

NEC® & CEC compliant

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	EMT Conduit Size	MC/AC Cable Size	Flange Thickness	Flexible Conduit Size
812MB1824CO	1/2", 3/4"		1/8"	
16MB1824CO	3/4", 1"		1/8"	
812MB1858CO	1/2", 3/4"		5/16" - 1/2"	
6MB1858CO		14-2 to 12-3	5/16" - 1/2"	3/8"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

