

B18 Combination Box/Conduit Hanger



The nVent CADDY B18 Combination Box/Conduit Hanger presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.

CERTIFICATIONS



FEATURES

Scoreline breakaway feature can be easily modified by hand while maintaining UL listing

Eliminates need for offset bending conduit

Designed to be versatile and reusable

Labor and time savings due to built-in first means of support

NEC® & CEC compliant

SPECIFICATIONS

Finish: Pregalvanized;nVent CADDY Armour

Material: Steel;Spring Steel

Table 1/2

Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Hole Size (HS)	Hole Type	Screw Included
16MB18A			3/4", 1"	1/4"	Plain	No


CatalogNumber	FlexibleConduit Size	MC/AC Cable Size	EMT Conduit Size	Hole Size (HS)	Hole Type	Screw Included
6MB18A	3/8"	14-2 to 12-3		1/4"	Plain	No
812MB18A			1/2", 3/4"	1/4"	Plain	No
812MB18S			1/2", 3/4"			Yes

Table 2/2				
Catalog Number	Screw Diameter (Sc)	Screw Length (L)	Length (L)	Width (W)
16MB18A			18"	2.1"
6MB18A			18"	2.1"
812MB18A			18"	2.1"
812MB18S	1/4"	9/16"	18"	2.1"

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

