

BC-M Conduit to Beam Clamp



CERTIFICATIONS





FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit

Conduit clip rotates 360 degrees

SPECIFICATIONS


Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1									
Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load (F)			
BC812M	1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	1/2" Max	20 ft·lbf	100lb			
BC16M	3/4", 1"	3/4", 1"	0.920" - 1.38"	1/2" Max	20 ft·lbf	100lb			

CatalogNumber	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load (F)
BC20M	1 1/4"	1 1/4"		1/2" Max	20 ft·lbf	100lb
BC24M	1 1/2"	1 1/2"	1 1/2"	1/2" Max	20 ft·lbf	100lb
BC32M	2"	2"		1/2" Max	20 ft·lbf	100lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOP

HOFFMAN

ILSCO SCHROFF

TRACHTE

