

# BC200/BC400 Beam Clamp



## CERTIFICATIONS



## FEATURES

Threaded hole on back and bottom

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel


Table 1/1

Catalog Number	Rod Size (RS)	Flange Thickness (FT)	Torque (TQ)	Static Load (F)
BC200	1/4"	1/2" Max	20 ft·lbf	100lbf
BC400	3/8"	3/4" Max	20 ft·lbf	200lbf

## ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

