

Bolt Close Conduit/Pipe Clamp



CERTIFICATIONS







FEATURES

Retained bolt and built-in nut means there are less parts to handle or drop

Combo head bolt works with slotted, hex, #3 phillips or #2 robertson drivers

SPECIFICATIONS

Table 1/2						
Catalog Number	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD2.5BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.220" - 1.51"	1 1/4"	
CD2BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.000" - 1.31"	1"	1"
CD3BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.410" - 1.74"	1 1/2"	1 1/4"

CatalogNumber	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD0B	Steel	Electrogalvaniz ed	Built-In Nut	0.670" - 0.84"	1/2"	1/2"
CDOBSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	0.670" - 0.84"	1/2"	1/2"
CD1B	Steel	Electrogalvaniz ed	Built-In Nut	0.740" - 1.05"	3/4"	3/4"
CD1BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	0.740" - 1.05"	3/4"	3/4"
CD2.5B	Steel	Electrogalvaniz ed	Built-In Nut	1.220" - 1.51"	1 1/4"	
CD2B	Steel	Electrogalvaniz ed	Built-In Nut	1.000" - 1.31"	1"	1"
CD3B	Steel	Electrogalvaniz ed	Built-In Nut	1.410" - 1.74"	1 1/2"	1 1/4"
CD4B	Steel	Electrogalvaniz ed	Built-In Nut	1 3/4" - 1.9"		1 1/2"
CD4BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1 3/4" - 1.9"		1 1/2"
CD5B	Steel	Electrogalvaniz ed	Built-In Nut	1.910" - 2.88"	2"	2"
CD5BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	1.910" - 2.88"	2"	2"
CD6B	Steel	Electrogalvaniz ed	Hex Nut	2.6" - 3"	2 1/2"	2 1/2"
CD7B	Steel	Electrogalvaniz ed	Hex Nut	3.150" - 3 1/2"	3"	3"
CD8B	Steel	Electrogalvaniz ed	Hex Nut	3.740" - 4.13"	3 1/2"	3 1/2"
CD9B	Steel	Electrogalvaniz ed	Hex Nut	4 1/4" - 4.53"	4"	4"
CD6BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	2.6" - 3"	2 1/2"	2 1/2"


CatalogNumber	Material	Finish	Nut Type	Outer Diameter (OD)	EMT Conduit Size	Rigid Conduit/Pipe Size
CD7BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	3.150" - 3 1/2"	3"	3"
CD8BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	3.740" - 4.13"	3 1/2"	3 1/2"
CD9BSS	Stainless Steel 304 (EN 1.4301)		Hex Nut	4 1/4" - 4.53"	4"	4"
CD0B37	Steel	Electrogalvaniz ed	Built-In Nut	0.670" - 0.84"	1/2"	1/2"
CD1B37	Steel	Electrogalvaniz ed	Built-In Nut	0.740" - 1.05"	3/4"	3/4"
CD2.5B37	Steel	Electrogalvaniz ed	Built-In Nut	1.220" - 1.51"	1 1/4"	
CD2B37	Steel	Electrogalvaniz ed	Built-In Nut	1.000" - 1.31"	1"	1"
CD3B37	Steel	Electrogalvaniz ed	Built-In Nut	1.410" - 1.74"	1 1/2"	1 1/4"
CD4B37	Steel	Electrogalvaniz ed	Built-In Nut	1 3/4" - 1.9"		1 1/2"
CD5B37	Steel	Electrogalvaniz ed	Built-In Nut	1.910" - 2.88"	2"	2"


Table 2/2						
Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications		
CD2.5BSS	0.27"	200lb	50lb	UL, cUL		
CD2BSS	0.27"	200lb	50lb			
CD3BSS	0.27"	200lb	50lb	UL, cUL		
CD0B	0.28"	200lb	50lb	UL, cUL		
CDOBSS	0.28"	200lb	50lb	UL, cUL		
CD1B	0.28"	200lb	50lb	cUL, ITB, UL		

Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD1BSS	0.28"	200lb	50lb	UL, cUL
CD2.5B	0.28"	200lb	50lb	cUL, UL
CD2B	0.28"	200lb	50lb	cUL, UL
CD3B	0.28"	200lb	50lb	UL, cUL, ITB
CD4B	0.28"	200lb	50lb	cUL, ITB, UL
CD4BSS	0.28"	200lb	50lb	UL, cUL
CD5B	0.28"	200lb	50lb	cUL, UL, ITB
CD5BSS	0.28"	350lb	50lb	cUL, UL
CD6B	5/16"	350lb	50lb	
CD7B	5/16"	350lb	50lb	
CD8B	5/16"	350lb	50lb	
CD9B	5/16"	350lb	50lb	
CD6BSS	0.33"	350lb	50lb	
CD7BSS	0.33"	350lb	50lb	
CD8BSS	0.33"	350lb	50lb	
CD9BSS	0.33"	350lb	50lb	
CD0B37	0.41"	200lb	50lb	
CD1B37	0.41"	200lb	50lb	

Catalog Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
CD2.5B37	0.41"	200lb	50lb	
CD2B37	0.41"	200lb	50lb	
CD3B37	0.41"	200lb	50lb	
CD4B37	0.41"	200lb	50lb	
CD5B37	0.41"	200lb	50lb	

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

