

Cable Spool



CERTIFICATIONS



FEATURES

Cut to length as needed

Pre-stretched restraint cable

Certified chemically compatible with CPVC piping systems

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Finish: Pregalvanized;Painted

Material: Steel

Table 1/1

Catalog Number	Brace Size	Diameter	Cable Length	UL Listed Load	Color
CSB12CBL	#12	3/32"	250'	418lb	Red

Catalog Number	Brace Size	Diameter	Cable Length	UL Listed Load	Color
CSB18CBL	#18	1/8"	250'	772lb	White
CSB36CBL	#36	3/16"	250'	1909lb	Blue

ADDITIONAL PRODUCT DETAILS

Cable is powder coated.

FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® piping systems and products made with TempRite® Technology.™ “The FBC System Compatible Logo, FBC™, FlowGuard Gold®, BlazeMaster®, Corzan®, and TempRite® are trademarks of Lubrizol Advanced Materials, Inc. or its affiliates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

