

Clevis Bolt Spacer



FEATURES

Seismically braces the 401 Clevis Hanger series for lateral load

Retrofit ability allows the spacer to be installed after the clevis and pipe are installed

Ears easily pinch closed around the clevis hanger cross bolt with pliers

FM® Specification Tested (up to 8" Pipe Size)

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel

Table 1/1

Catalog Number	Pipe Size	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0100	1"	1.21"	0.51"	0.07"	0.51"
CSBCS0125	1 1/4" Min	1.55"	0.51"	0.07"	0.51"
CSBCS0150	1 1/2"	1.71"	0.51"	0.07"	0.51"
CSBCS0200	2" Min	2.28"	0.51"	0.07"	0.51"
CSBCS0250	2 1/2"	2.78"	0.67"	0.07"	0.65"

Catalog Number	Pipe Size	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0300	3"	3.41"	0.67"	0.07"	0.65"
CSBCS0350	3 1/2"	3.91"	0.67"	0.07"	0.65"
CSBCS0400	4"	4.41"	0.67"	0.07"	0.65"
CSBCS0500	5"	5 1/2"	0.98"	0.07"	0.9"
CSBCS0600	6"	6.56"	0.98"	0.07"	0.9"
CSBCS0800	8"	8.56"	1.22"	0.07"	1.09"
CSBCS1000	10"	10.52"	1.22"	0.07"	1.09"
CSBCS1200	12"	12.52"	1.22"	0.07"	1.09"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

