

Conduit Trapeze CCT2



The nVent CADDY Conduit Trapeze CCT2 range is a fast and cost-effective method to install smaller feeder circuits of conduit in overhead trapeze installations. The CCT2 series eliminates reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

CERTIFICATIONS





FEATURES

Ideal for larger branch circuits

Accommodates ½ in threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239

SPECIFICATIONS

EMT Conduit Size: 2"
Rigid Conduit Size: 2"
Material: Steel

Table 1/2							
Catalog Number	Number of Conduits	Rod Size (RS)	Thickness (T)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Hole Size 3 (HS3)	
CCT2X12	4	1/2"	16ga	0.56"	0.28"	0.12"	

CatalogNumber	Number of Conduits	Rod Size (RS)	Thickness (T)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Hole Size 3 (HS3)	
CCT2X24	8	1/2"	16ga	0.56"	0.28"	0.12"	
CCT2X36	12	1/2"	16ga	0.56"	0.28"	0.12"	
CCT2X96	32	1/2"	16ga	0.56"	0.28"	0.12"	


Table 2/2							
Catalog Number	Hole Size 4 (HS4)	Length 1 (L1)	Length 2 (L2)	Length 3 (L3)	Length 4 (L4)	Length (L)	
CCT2X12	2.38"	12"	14"	3"	3"	14"	
CCT2X24	2.38"	24"	26"	3"	3"	26"	
CCT2X36	2.38"	36"	38"	3"	3"	38"	
CCT2X96	2.38"	96"	98"	3"	3"	98"	

ADDITIONAL PRODUCT DETAILS

For 1/2" threaded rod trapeze drops, use washer or SN50.

The table contains maximum conduit size values.

UL Load Rating										
Orientation	Mounting Fastener	Fastener	Fastener Spacing							
		6"	12"	18"	24"	30"	36"	42"	48"	
Horizontal	1/2" Threaded Rod	500 lb	500 lb	400 lb	300 lb	275 lb	250 lb	225 lb	200 lb	
Vertical	1/2" Fastener	600 lb	600 lb	-	-	-	-	-	-	
Evenly Distributed Load Rating										
Horizontal	1/2"	-	720 lb	600 lb	475 lb	425 lb	375 lb	325 lb	300 lb	



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

