

# Deck Screw



## FEATURES

Secures nVent CADDY Pyramid Rooftop Anchors to various roof substrate materials

## SPECIFICATIONS

**Color:** Black  
**Finish:** Epoxy Coated  
**Material:** Steel

Table 1/1

Catalog Number	Screw Diameter	Screw Length
A927W001P100	14	2"
A927W008P100	15	2"
A927W002P100	14	3"
A927W009P100	15	3"
A927W003P100	14	4"
A927W010P100	15	4"

Catalog Number	Screw Diameter	Screw Length
A927W004P100	14	5"
A927W011P100	15	5"
A927W005P100	14	6"
A927W012P100	15	6"
A927W006P100	14	7"
A927W013P100	15	7"
A927W007P100	14	8"
A927W014P100	15	8"
A927W019P100	15	9"
A927W016P100	14	10"
A927W020P100	15	10"
A927W018P100	14	12"
A927W021P100	15	12"
A927W022P100	15	14"

## ADDITIONAL PRODUCT DETAILS

#14 deck screws are for general purpose use.

#15 deck screws are specially suited for OSB and light gauge steel.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

