

# **EM-M Conduit/Pipe to Flange Clip**



## **CERTIFICATIONS**





## **FEATURES**

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

## **SPECIFICATIONS**

Finish: nVent CADDY Armour

Material: Spring Steel


| Table 1/2         |                     |                               |                     |                     |                          |                          |
|-------------------|---------------------|-------------------------------|---------------------|---------------------|--------------------------|--------------------------|
| Catalog<br>Number | EMT Conduit<br>Size | Rigid<br>Conduit/Pipe<br>Size | MC/AC Cable<br>Size | Outer Diameter (OD) | Flange<br>Thickness (FT) | Flexible<br>Conduit Size |
| 16M24             | 3/4", 1"            | 3/4", 1"                      |                     | 0.920" - 1.38"      | 1/8" - 1/4"              |                          |
| 20M24             | 1 1/4"              | 1 1/4"                        |                     | 1.380" - 1.65"      | 1/8" - 1/4"              |                          |

| CatalogNumber | EMT Conduit<br>Size | Rigid<br>Conduit/Pipe<br>Size | MC/AC Cable<br>Size | Outer Diameter (OD) | Flange<br>Thickness (FT) | FlexibleConduit<br>Size |
|---------------|---------------------|-------------------------------|---------------------|---------------------|--------------------------|-------------------------|
| 24M24         | 1 1/2"              | 1 1/2"                        |                     | 1.650" - 1.97"      | 1/8" - 1/4"              |                         |
| 32M24         | 2"                  | 2"                            |                     | 1.970" - 2.36"      | 1/8" - 1/4"              |                         |
| 6M24          |                     | 3/8"                          | 14-2 to 12-3        | 0.550" - 0.71"      | 1/8" - 1/4"              | 3/8"                    |
| 812M24        | 1/2", 3/4"          | 1/2", 3/4"                    |                     | 0.710" - 1.18"      | 1/8" - 1/4"              |                         |
| 16M58         | 3/4", 1"            | 3/4", 1"                      |                     | 0.920" - 1.38"      | 5/16" - 1/2"             |                         |
| 20M58         | 1 1/4"              | 1 1/4"                        |                     | 1.380" - 1.65"      | 5/16" - 1/2"             |                         |
| 24M58         | 1 1/2"              | 1 1/2"                        |                     | 1.650" - 1.97"      | 5/16" - 1/2"             |                         |
| 32M58         | 2"                  | 2"                            |                     | 1.970" - 2.36"      | 5/16" - 1/2"             |                         |
| 6M58          |                     | 3/8"                          | 14-2 to 12-3        | 0.550" - 0.71"      | 5/16" - 1/2"             | 3/8"                    |
| 812M58        | 1/2", 3/4"          | 1/2", 3/4"                    |                     | 0.710" - 1.18"      | 5/16" - 1/2"             |                         |
| 6M912         |                     | 3/8"                          | 14-2 to 12-3        | 0.550" - 0.71"      | 9/16" - 3/4"             | 3/8"                    |
| 812M1318      | 1/2", 3/4"          | 1/2", 3/4"                    |                     | 0.710" - 1.18"      | 13/16" - 1 1/8"          |                         |
| 812M912       | 1/2", 3/4"          | 1/2", 3/4"                    |                     | 0.710" - 1.18"      | 9/16" - 3/4"             |                         |
| 16M912        | 3/4", 1"            | 3/4", 1"                      |                     | 0.920" - 1.38"      | 9/16" - 3/4"             |                         |
| 20M912        | 1 1/4"              | 1 1/4"                        |                     | 1.380" - 1.65"      | 9/16" - 3/4"             |                         |
| 24M912        | 1 1/2"              | 1 1/2"                        |                     | 1.650" - 1.97"      | 9/16" - 3/4"             |                         |
| 32M912        | 2"                  | 2"                            |                     | 1.970" - 2.36"      | 9/16" - 3/4"             |                         |

| Table 2/2      |                 |                |  |  |  |  |
|----------------|-----------------|----------------|--|--|--|--|
| Catalog Number | Static Load (F) | Certifications |  |  |  |  |
| 16M24          | 75lb            |                |  |  |  |  |
| 20M24          | 75lb            |                |  |  |  |  |
| 24M24          | 75lb            |                |  |  |  |  |
| 32M24          | 75lb            |                |  |  |  |  |
| 6M24           | 75lb            |                |  |  |  |  |
| 812M24         | 75lb            |                |  |  |  |  |
| 16M58          | 75lb            |                |  |  |  |  |
| 20M58          | 75lb            |                |  |  |  |  |
| 24M58          | 75lb            |                |  |  |  |  |
| 32M58          | 75lb            |                |  |  |  |  |
| 6M58           | 75lb            |                |  |  |  |  |
| 812M58         | 75lb            |                |  |  |  |  |
| 6M912          | 75lb            |                |  |  |  |  |
| 812M1318       | 75lb            | UL, cUL        |  |  |  |  |
| 812M912        | 75lb            |                |  |  |  |  |
| 16M912         | 75lb            |                |  |  |  |  |
| 20M912         | 75lb            |                |  |  |  |  |
| 24M912         | 75lb            | UL, cUL        |  |  |  |  |

| Catalog Number | Static Load (F) | Certifications |
|----------------|-----------------|----------------|
| 32M912         | 75lb            |                |

#### **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

# North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ER

ERICO F

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.