

ESC-M Conduit to Strut Clip



CERTIFICATIONS



FEATURES

Attaches to open side of a strut channel

Includes easy close pipe and conduit clamp

SPECIFICATIONS

Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/2

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	MC/AC Cable Size	Flexible Conduit Size	Outer Diameter (OD)	Flange Thickness (FT)
ESC6M		3/8"	14-2 to 12-3	3/8"	0.550" - 0.71"	3/8"
ESC812M	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	3/8"

Table 2/2		
Catalog Number	Static Load (F)	Certifications
ESC6M	25lb	
ESC812M	25lb	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

