

Free Spring Mount



The Vibration Isolation Mount line from nVent CADDY is used to minimize vibrations produced by supported systems such as mechanical equipment, pumps, ductwork, piping, and in-line, exhaust and cabinet fans.

FEATURES

Used to support HVAC equipment, air conditioning units, compressors, pumps, chillers and cooling towers

Spring elements are color coded for accurate selection and easy field verification

Rubber surface provides anti-skid properties

Built-in leveling device allows for fine-tuning adjustment

SPECIFICATIONS

Table 1/1

Catalog Number	Length	Width	Height	Ultimate Static Load	Deflection
VIBFSM1A050	2.875"	5"	5.5"	50lb	1"
VIBFSM1A100	2.875"	5"	5.5"	100lb	1"
VIBFSM1A1000	2.875"	5"	5.5"	1000lb	1"
VIBFSM1A1100	2.875"	5"	5.5"	1100lb	1"
VIBFSM1A1200	2.875"	5"	5.5"	1200lb	1"
VIBFSM1A200	2.875"	5"	5.5"	200lb	1"

Catalog Number	Length	Width	Height	Ultimate Static Load	Deflection
VIBFSM1A300	2.875"	5"	5.5"	300lb	1"
VIBFSM1A400	2.875"	5"	5.5"	400lb	1"
VIBFSM1A500	2.875"	5"	5.5"	500lb	1"
VIBFSM1A600	2.875"	5"	5.5"	600lb	1"
VIBFSM1A700	2.875"	5"	5.5"	700lb	1"
VIBFSM1A800	2.875"	5"	5.5"	800lb	1"
VIBFSM1A900	2.875"	5"	5.5"	900lb	1"
VIBFSM1B1000	4"	6"	4.875"	1000lb	1"
VIBFSM1B1200	4"	6"	4.875"	1200lb	1"
VIBFSM1B1400	4"	6"	4.875"	1400lb	1"
VIBFSM1B150	4"	6"	4.875"	150lb	1"
VIBFSM1B1600	4"	6"	4.875"	1600lb	1"
VIBFSM1B1800	4"	6"	4.875"	1800lb	1"
VIBFSM1B2000	4"	6"	4.875"	2000lb	1"
VIBFSM1B2200	4"	6"	4.875"	2200lb	1"
VIBFSM1B2500	4"	6"	4.875"	2500lb	1"
VIBFSM1B300	4"	6"	4.875"	300lb	1"
VIBFSM1B400	4"	6"	4.875"	400lb	1"

Catalog Number	Length	Width	Height	Ultimate Static Load	Deflection
VIBFSM1B600	4"	6"	4.875"	600lb	1"
VIBFSM1B800	4"	6"	4.875"	800lb	1"
VIBFSM2A050	2.875"	5"	7.875"	50lb	2"
VIBFSM2A100	2.875"	5"	7.875"	100lb	2"
VIBFSM2A1000	2.875"	5"	7.875"	1000lb	2"
VIBFSM2A1100	2.875"	5"	7.875"	1100lb	2"
VIBFSM2A1200	2.875"	5"	7.875"	1200lb	2"
VIBFSM2A200	2.875"	5"	7.875"	200lb	2"
VIBFSM2A300	2.875"	5"	7.875"	300lb	2"
VIBFSM2A400	2.875"	5"	7.875"	400lb	2"
VIBFSM2A500	2.875"	5"	7.875"	500lb	2"
VIBFSM2A600	2.875"	5"	7.875"	600lb	2"
VIBFSM2A700	2.875"	5"	7.875"	700lb	2"
VIBFSM2A800	2.875"	5"	7.875"	800lb	2"
VIBFSM2A900	2.875"	5"	7.875"	900lb	2"
VIBFSM2B1000	4"	6"	7.25"	1000lb	2"
VIBFSM2B1200	4"	6"	7.25"	1200lb	2"
VIBFSM2B1400	4"	6"	7.25"	1400lb	2"

Catalog Number	Length	Width	Height	Ultimate Static Load	Deflection
VIBFSM2B150	4"	6"	7.25"	150lb	2"
VIBFSM2B1600	4"	6"	7.25"	1600lb	2"
VIBFSM2B1800	4"	6"	7.25"	1800lb	2"
VIBFSM2B2000	4"	6"	7.25"	2000lb	2"
VIBFSM2B2200	4"	6"	7.25"	2200lb	2"
VIBFSM2B2500	4"	6"	7.25"	2500lb	2"
VIBFSM2B300	4"	6"	7.25"	300lb	2"
VIBFSM2B400	4"	6"	7.25"	400lb	2"
VIBFSM2B600	4"	6"	7.25"	600lb	2"
VIBFSM2B800	4"	6"	7.25"	800lb	2"

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

