

# H-MSM Conduit/Pipe to Flange Clip, Side Mount



## **CERTIFICATIONS**







## **FEATURES**

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

## **SPECIFICATIONS**

Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/2						
Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Flexible Conduit Size	MC/AC Cable Size	Outer Diameter (OD)	Flange Thickness (FT)
16M24SM	3/4", 1"	3/4", 1"			0.920" - 1.38"	1/8"
20M24SM	1 1/4"	1 1/4"			1.380" - 1.65"	1/8"

CatalogNumber	EMT Conduit Size	Rigid Conduit/Pipe Size	FlexibleConduit Size	MC/AC Cable Size	Outer Diameter (OD)	Flange Thickness (FT)
24M24SM	1 1/2"	1 1/2"			1.650" - 1.97"	1/8"
32M24SM	2"	2"			1.970" - 2.36"	1/8"
6M24SM		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	1/8"
812M24SM	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	1/8"
16M58SM	3/4", 1"	3/4", 1"			0.920" - 1.38"	5/16" - 1/2"
20M58SM	1 1/4"	1 1/4"			1.380" - 1.65"	5/16" - 1/2"
24M58SM	1 1/2"	1 1/2"			1.650" - 1.97"	5/16" - 1/2"
32M58SM	2"	2"			1.970" - 2.36"	5/16" - 1/2"
6M58SM		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	5/16" - 1/2"
812M58SM	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	5/16" - 1/2"
6M912SM		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	9/16" - 3/4"
812M912SM	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	9/16" - 3/4"
16M912SM	3/4", 1"	3/4", 1"			0.920" - 1.38"	9/16" - 3/4"
20M912SM	1 1/4"	1 1/4"			1.380" - 1.65"	9/16" - 3/4"
24M912SM	1 1/2"	1 1/2"			1.650" - 1.97"	9/16" - 3/4"
32M912SM	2"	2"			1.970" - 2.36"	9/16" - 3/4"

Table 2/2				
Catalog Number	Static Load (F)	Certifications		

16M24SM	25lb	UL, cUL
20M24SM	25lb	cUL, UL
24M24SM	25lb	cUL, UL
32M24SM	25lb	UL, cUL
6M24SM	25lb	UL, cUL
812M24SM	25lb	UL, cUL, ITB
16M58SM	25lb	UL, cUL
20M58SM	25lb	
24M58SM	25lb	cUL, UL
32M58SM	25lb	UL, cUL
6M58SM	25lb	UL, cUL
812M58SM	25lb	cUL, ITB, UL
6M912SM	25lb	
812M912SM	25lb	UL, cUL, ITB
16M912SM	25lb	cUL, UL
20M912SM	25lb	
24M912SM	25lb	cUL, UL
32M912SM	25lb	cUL, UL



### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.