

H-MSMR Conduit to Flange Clip with Retainer, Side Mount



FEATURES

Only one piece to install

Fast hammer-on installation

Pre-riveted retainer strap is easily bent into position

Lightweight design

SPECIFICATIONS


Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1											
Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Flange Thickness (FT)	Length (L)	Static Load (F)					
C2416SM	3/4", 1"	3/4", 1"	0.920" - 1.38"	1/8"	13"	25lb					
C58812SM	1/2", 3/4"	1/2", 3/4"	0.700" - 1.18"	5/16" - 1/2"	7.85"	25lb					
C5816SM	3/4", 1"	3/4", 1"	0.920" - 1.38"	5/16" - 1/2"	13"	25lb					
C912812SM	1/2", 3/4"	1/2", 3/4"	0.700" - 1.18"	9/16" - 3/4"	7.85"	25lb					

CatalogNumber	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Flange Thickness (FT)	Length (L)	Static Load (F)	
C91216SM	3/4", 1"	3/4", 1"	0.920" - 1.38"	9/16" - 3/4"	13"	25lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO S

SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.