

# H-PSM Conduit to Flange Clip, Side Mount



### **CERTIFICATIONS**



# **FEATURES**

Requires only a hammer to install

Available for EMT, rigid and aluminum conduit

Will pivot thru 360°

# **SPECIFICATIONS**

**Finish:** nVent CADDY Armour


Orientation: Side Mount

Material: Spring Steel

Table 1/1						
Catalog Number	EMT Conduit Size	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)		
16P24SM	1"	1.180" - 1.38"	1/8"	25lb		
8P24SM	1/2"	0.710" - 0.87"	1/8"	25lb		

Catalog Number	EMT Conduit Size	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)
12P24SM	3/4"	0.870" - 1.18"	1/8"	25lb
8P58SM	1/2"	0.710" - 0.87"	5/16" - 1/2"	25lb
16P58SM	1"	1.180" - 1.38"	5/16" - 1/2"	25lb
12P58SM	3/4"	0.870" - 1.18"	5/16" - 1/2"	25lb
8P912SM	1/2"	0.710" - 0.87"	9/16" - 3/4"	25lb
12P912SM	3/4"	0.870" - 1.18"	9/16" - 3/4"	25lb
16P912SM	1"	1.180" - 1.38"	9/16" - 3/4"	25lb

### **DIAGRAMS**



# WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

