

Hammer-On Flange Clip, Bottom Mount



CERTIFICATIONS







FEATURES

Can be used to support boxes, fixtures or other applications from beam flanges

Assorted attachment points provided to reduce inventory

Requires only a hammer to install

SPECIFICATIONS


Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/1								
Catalog Number	Flange Thickness (FT)	Rod Size (RS)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)			
M24	1/8" - 1/4"	1/4"	100lb	25lb	75lb			
M912	9/16" - 3/4"	1/4"	100lb	25lb	75lb			

Catalog Number	Flange Thickness (FT)	Rod Size (RS)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
M1318	13/16" - 1 1/8"	1/4"	100lb	25lb	75lb
M58	5/16" - 1/2"	1/4"	100lb	25lb	75lb

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

