

HangerMate® Vertical Mount Screw for Concrete



FEATURES

End-drilled and tapped for attaching threaded components to concrete

Solid, one piece cold formed part; head cannot spin off or unscrew from body

Tapered threads allow for easy starting in pre-drilled hole

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Rod Size	Screw Diameter	Screw Length	Drill Bit Diameter	Ultimate Static Load
HMZG365	1/4"	5/16"	2 1/4"	1/4"	2188lb
HMZG730	3/8"	5/16"	2 1/4"	1/4"	2188lb

ADDITIONAL PRODUCT DETAILS

Tested in 3650 psi concrete.

Appropriate safety factors should be applied for design purposes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

