

Improved nVent CADDY Cat HP J-Hook Mod Clip with BC200 Beam Clamp



The Improved nVent CADDY Cat HP Mod Clip J-Hook with BC200 Beam Clamp eliminates the need for screws, rivets, or special tools—significantly cutting down installation time and expense. Contractors gain a secure hold on J-Hooks, boosting stability and flexibility on-site while minimizing inventory impact.

CERTIFICATIONS





FEATURES


Easy beam flange installation

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

SPECIFICATIONS

Table 1/1				
Catalog Number	Finish	Material	Flange Thickness (FT)	Static Load (F)
CATHPMBC200	Electrogalvanized, nVent CADDY Armour	Steel, Spring Steel	0.125" - 0.625"	100lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF **TRACHTE**

