

# Improved nVent CADDY Cat HP J-Hook Mod Clip with Hammer-On Flange Clip



The Improved nVent CADDY Cat HP Mod Clip J-Hook Clip with Hammer-On Flange Clip simplifies beam flange installation with an easy-to-use design. By eliminating the need for screws, rivets or special tools during assembly, installation time and cost is reduced. A simple clip onto nVent CADDY Cat HP components ensures a secure hold—ultimately enhancing rigidity and stability while minimizing inventory impact and providing flexibility on the job site.

# **CERTIFICATIONS**





# **FEATURES**

Requires only a hammer to install

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

## **SPECIFICATIONS**

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1		
Catalog Number	Flange Thickness (FT)	Static Load (F)
CATHPM58SM	0.3" - 0.5"	200lb
CATHPM912SM	0.56" - 0.75"	200lb



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 

