


Improved nVent CADDY Cat HP J-Hook Mod Clip with Straight Bracket



Improved nVent CADDY Cat HP Mod Clip J-Hook Straight Bracket offers surface attachment flexibility without requiring screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CERTIFICATIONS



FEATURES

Can be attached to various nVent CADDY fasteners or screwed directly to a wall

Ideal for attaching to concrete, steel or wood surfaces

Works with nVent J-Hook Versa-Mount technology from nVent CADDY


No screws, rivets or special tools required for assembly

SPECIFICATIONS

Table 1/1

Catalog Number	Finish	Material	Hole Size (HS)	Static Load (F)
CATHPMS4	nVent CADDY Armour	Spring Steel	0.25"	200lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

