

MC/AC Cable Support Bracket



CERTIFICATIONS



BABA



FEATURES

Neatly isolates, supports and secures MC/AC cables

Properly spaces MC/AC cable to help eliminate bundling and NEC® & CEC derating issues

Results in a "neat and workmanlike" installation

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

| Catalog Number | Isolated Ground Cable Size | MC/AC Cable Size | Super Neutral Cable Size | Cable Capacity | Hole Size 1 (HS1) | Hole Size 2 (HS2) |
|----------------|----------------------------|------------------|--------------------------|----------------|-------------------|-------------------|
| MCS100 | | 14-3 to 10-2 | 10-2 | 8 | 1/4" | 0.2" |
| MCS101 | 12-3 to 8-2 | 10-3 to 8-3 | 12-3 to 10-2 | 7 | 1/4" | 0.2" |


| CatalogNumber | IsolatedGround CableSize | MC/AC Cable Size | Super Neutral Cable Size | Cable Capacity | Hole Size 1 (HS1) | Hole Size 2 (HS2) |
|---------------|-----------------------------|---------------------|-----------------------------|----------------|----------------------|----------------------|
| MCS50 | | 14-3 to 10-2 | 10-2 | 4 | 1/4" | 0.2" |

| Table 2/2 | |
|----------------|---------------------|
| Catalog Number | Outer Diameter (OD) |
| MCS100 | 0.430" - 0.56" |
| MCS101 | 0.560" - 0.69" |
| MCS50 | 0.430" - 0.56" |

ADDITIONAL PRODUCT DETAILS

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

