

Multi-Function Clip





CERTIFICATIONS







FEATURES

Provides attachment of electrical boxes

Supports #10-24 and 1/4-20 (M6) threaded bridle rings

Instills more confidence installing conduit, MC/AC, and low voltage applications

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/2						
Catalog Number	Rod Size (RS)	Wire Size	Flange Thickness (FT)	Hole Size (HS)	Screw Included	Screw Diameter (Sc)
4Z4S	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"		Yes	1/4"
4Z34	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"	1/4"	No	

CatalogNumber	Rod Size (RS)	Wire Size	Flange Thickness (FT)	Hole Size (HS)	Screw Included	ScrewDiameter (Sc)
8Z34	1/2", 5/8"	#1		1/4"	No	
8Z4S	1/2", 5/8"	#1			Yes	1/4"


Table 2/2						
Catalog Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications			
4Z4S	25lb	20lb	cUL, UL			
4Z34	25lb	20lb	cUL, ITB, UL			
8Z34		50lb	cUL, UL			
8Z4S		50lb	cUL, UL			

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod and EC311.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

