


NM Cable to Beam Clamp



CERTIFICATIONS



FEATURES

Supports non-metallic sheathed cable with ground wire


SPECIFICATIONS

Table 1/1						
Catalog Number	Material	Finish	NM Cable Size	Outer Diameter (OD)	Flange Thickness (FT)	Height (H)
RMXBC	Spring Steel	nVent CADDY Armour	14-2, 12-2	0.280" - 0.32"	1/2" Max	2.18"

ADDITIONAL PRODUCT DETAILS

Assemblies allow support from most main and substructures.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

