

# No Pry Clip



## **CERTIFICATIONS**











## **FEATURES**

Eliminates prying effect on fasteners and anchors

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

#### **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel


Table 1/1				
Catalog Number	Brace Size	Hole Size (HS)	UL Listed Load	
CSBNPC38	#12, #18, #36	7/16"	1909lb	
CSBNPC12	#12, #18, #36	9/16"	1909lb	

# **ADDITIONAL PRODUCT DETAILS**

Brace member is not included.

UL Loads			
Part Number	Brace Member	Load Rating	
	CSB12CBL	418 lb	
CSBNPC38	CSB18CBL	772 lb	
	CSB36CBL	1910 lb	
	CSB12CBL	418 lb	
CSBNPC12	CSB18CBL	772 lb	
	CSB36CBL	1910 lb	

#### **DIAGRAMS**



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 

