

nVent CADDY All-in-One Between-Stud With Removable Mud Ring, Single Box



CERTIFICATIONS





FEATURES

Removable mud ring provides front access to the interior of the box

Box remains fixed in place when mud ring is removed

Pre-bent tabs on support bracket help to quickly square assembly to stud

Center marks provide easy height positioning

Includes multiple $\frac{1}{2}$ and $\frac{3}{4}$ in knockouts on each side of the box

SPECIFICATIONS

Knockout Sizes: (8) 1/2", 3/4";(3) 1/2"

Finish: Pregalvanized

Material: Steel

Table 1/2						
Catalog Number	Gang	Ground Wire Included	Box Volume	Drywall Thickness	Stud Spacing	Depth (D)

A1BF2G	2	Yes	32.8in³	5/8"	16" - 24"	3 5/8"
A1BF1G	1	Yes	32.8in³	5/8"	16" - 24"	3 5/8"
A1BF3G	1	Yes	32.8in³	1 1/4"	16" - 24"	3 5/8"

Table 2/2						
Catalog Number	A	В				
A1BF2G	5 3/8"	4 1/8"				
A1BF1G	5 3/8"	4 1/8"				
A1BF3G	5 3/8"	4 1/8"				

ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

24" stud spacing requires use of three mounting screws.

Use only with nVent CADDY All-in-One box assemblies.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

