

# nVent CADDY BCSP Box/Conduit Securement Platform Assembly



## FEATURES

Ideal single-rod securement for box/conduit installations

Accommodates a wide range of electrical boxes

Contains embedded rivet nut – no penetrating the electrical box

Tool-free securement options

## SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Steel

Table 1/1

Catalog Number	Knockout Sizes	Box Depth	Box Size	Box Volume	Ground Wire Included	Rod Size
SP45R254D	(4) 1/2", 3/4", (8) 1/2"	2.12"	4"	30.3in <sup>3</sup>	Yes	1/4"
SP45R25D5	(4) 1", 1-1/4", (1) 1/2"	2 7/8"	5"	67in <sup>3</sup>	Yes	1/4"
SP45R25P1	(12) 1/2", 3/4"	2.12"	4 11/16"	42in <sup>3</sup>	Yes	1/4"
SP454D	(4) 1/2", 3/4", (8) 1/2"	2.12"	4"	30.3in <sup>3</sup>	Yes	3/8"

CatalogNumber	Knockout Sizes	Box Depth	Box Size	Box Volume	Ground Wire Included	Rod Size
SP45D5	(4) 1", 1-1/4", (1) 1/2"	2 7/8"	5"	67in <sup>3</sup>	Yes	3/8"
SP45P1	(12) 1/2", 3/4"	2.12"	4 11/16"	42in <sup>3</sup>	Yes	3/8"
SP612AS08		4"	8"		Yes	3/8"
SP612AS12		4"	12"		Yes	3/8"
SP612RB08		3"	8"	179in <sup>3</sup>	Yes	3/8"
SP612RB12		4"	12"	546in <sup>3</sup>	Yes	3/8"

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

