

nVent CADDY Cat HP J-Hook Tree, Wall Mount



FEATURES

Ideal for attaching to concrete, steel or wood surfaces

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Ready to use out of the box, saving installation time and labor

Requires no screws, rivets or special tools for assembly

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized **Type:** Single Sided

Material: Steel

Table 1/2							
Catalog Number	Diameter (Ø)	Tiers	Height (H)	Width (W)	Hole Size (HS)	Static Load (F)	
CAT64HPSWM 2	4"	2	19 1/2"	2"	1/4"	120lb	
CAT32HPSWM 4	2"	4	24 1/2"	2"	1/4"	240lb	


CatalogNumber	Diameter (Ø)	Tiers	Height (H)	Width (W)	Hole Size (HS)	Static Load (F)
CAT64HPSWM 3	4"	3	27"	2"	1/4"	180lb
CAT32HPSWM 3	2"	3	19 1/2"	2"	1/4"	180lb
CAT32HPSWM 2	2"	2	14 1/2"	2"	1/4"	120lb
CAT64HPSWM 4	4"	4	34 1/2"	2"	1/4"	240lb


Table 2/2					
Catalog Number	Depth (D)				
CAT64HPSWM2	5 1/2"				
CAT32HPSWM4	3 3/8"				
CAT64HPSWM3	5 1/2"				
CAT32HPSWM3	3 3/8"				
CAT32HPSWM2	3 3/8"				
CAT64HPSWM4	5 1/2"				

ADDITIONAL PRODUCT DETAILS

Static loads represent maximum load limit of J-Hook tree. Static load limit of each J-Hook is 60 lb (270 N).

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

