

# nVent CADDY Flat Rigid Box Support Bracket Between Stud Assembly



## FEATURES

Stamped with A- and B-side markings that allow mounting for all box types and configurations – no need for removal of screws – simply flip and it's ready to use

Bracket is completely flat, no offset

Floor stand positions boxes 18 1/2" from the floor for consistent placement

## SPECIFICATIONS

**Knockout Sizes, Box 2:** (12) 1/2", 3/4"

**Knockout Sizes, Box 1:** (4) 1/2", 3/4";(8) 1/2"

**Finish:** Pregalvanized

**Material:** Steel

Table 1/3

Catalog Number	Box Depth	Box Size 1	Box Size 2	Drywall Thickness	Gang, Box 1	Gang, Box 2
F3A4DM10P1M 5	2.12"	4"	4 11/16"	3/4"	1	1
F3A4D0P1	2.12"	4"	4 11/16"			

Table 2/3

Catalog Number	Ground Wire Included, Box 1	Ground Wire Included, Box 2	Mud Ring Type	Position, Box 1	Position, Box 2	Stud Spacing
F3A4DM10P1M5	Yes	Yes	Raised	Left	Right	8" - 16"
F3A4D0P1	Yes	Yes		Left	Right	8" - 16"

Table 3/3

Catalog Number	Volume, Box 1	Volume, Box 2
F3A4DM10P1M5	30.3in <sup>3</sup>	42in <sup>3</sup>
F3A4D0P1	30.3in <sup>3</sup>	42in <sup>3</sup>

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

