

# **nVent CADDY Flexible Conduit Connector**



The nVent CADDY Flexible Conduit Connectors are a tool-free line of connectors built to accommodate a wide range of flexible conduit (14/2 to 10/2). Designed to form an easy, secure, snap-in connection, the connectors also provide the option for a quick, damage-free removal by simply depressing the side tab and rotating the fitting to remove cables without harm. In addition, the unique three-prong design assists in keeping the cable secure to reduce the risk of accidental disconnection or pullout.

### **CERTIFICATIONS**





### **FEATURES**

Innovative snap-in style design makes installing fitting to 1/2" box knockout fast and easy

Fitting can be easily removed by pressing tabs to release from box

Features ability to remove cables damage-free by simply twisting the fitting off cables

No tools required for installation


Offers insulated throat


Designed for AC, MCI-A, HCF steel and aluminum cable, flexible metal conduit steel and aluminum, MCI Cable, and continuous corrugated aluminum

Patented

## **SPECIFICATIONS**

| Table 1/1         |                        |                |              |            |           |            |
|-------------------|------------------------|----------------|--------------|------------|-----------|------------|
| Catalog<br>Number | Material               | Knockout Sizes | Diameter (Ø) | Length (L) | Width (W) | Height (H) |
| EZF1410           | Steel, Spring<br>Steel | 1/2"           | 0.37"        | 1.54"      | 1"        | 0.86"      |





### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC** 

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

TRACHTE

