


nVent CADDY Heavy Duty Box Support Bracket Between Stud Assembly



FEATURES

Heavy duty design with increased strength that is twice as strong than the first generation rigid box support

Accepts vertically or horizontally mounted single and double gang adjustable mud rings

Designed to work with snap in place first means of support for conduit and cables

SPECIFICATIONS

Knockout Sizes, Box 1: (4) 1/2", 3/4";(8) 1/2"

Finish: Pregalvanized

Material: Steel

Table 1/4

Catalog Number	Knockout Sizes, Box 2	Knockout Sizes, Box 3	Box Depth	Box Size 1	Box Size 2	Box Size 3
R34DM100			2.12"	4"		
R34DM10P1M5	(12) 1/2", 3/4"		2.12"	4"	4 11/16"	
R34DM200			2.12"	4"		
R34DV100			2.12"	4"		

CatalogNumber	KnockoutSizes, Box 2	KnockoutSizes, Box 3	Box Depth	Box Size 1	Box Size 2	Box Size 3
R34DV200			2.12"	4"		
R34D00			2.12"	4"		
R34D0D1	(4) 1", (4) 1 1/4"		2.12"	4"	4 11/16"	
R34D0P1	(12) 1/2", 3/4"		2.12"	4"	4 11/16"	
R44D4D0D1	(4) 1/2", 3/4", (8) 1/2"	(4) 1", (4) 1 1/4"	2.12"	4"	4"	4 11/16"

Table 2/4

Catalog Number	Drywall Thickness	Gang, Box 1	Gang, Box 2	Ground Wire Included, Box 1	Ground Wire Included, Box 2	Ground Wire Included, Box 3
R34DM100	3/4"	1		Yes		
R34DM10P1M5	3/4"	1	1	Yes	Yes	
R34DM200	3/4"	2		Yes		
R34DV100	3/4" - 1 1/2"	1		Yes		
R34DV200	3/4" - 1 1/2"	2		Yes		
R34D00				Yes		
R34D0D1				Yes	No	
R34D0P1				Yes	Yes	
R44D4D0D1				Yes	Yes	No

Table 3/4

Catalog Number	Mud Ring Type	Position, Box 1	Position, Box 2	Position, Box 3	Stud Spacing	Volume, Box 1
R34DM100	Raised	Left			16"	30.3in ³

CatalogNumber	Mud Ring Type	Position, Box 1	Position, Box 2	Position, Box 3	Stud Spacing	Volume, Box 1
R34DM10P1M5	Raised	Left	Right		16"	30.3in ³
R34DM200	Raised	Left			16"	30.3in ³
R34DV100	Adjustable	Left			16"	30.3in ³
R34DV200	Adjustable	Left			16"	30.3in ³
R34D00		Left			16"	30.3in ³
R34D0D1		Left	Right		16"	30.3in ³
R34D0P1		Left	Right		16"	30.3in ³
R44D4D0D1		Left	Middle	Right	24"	30.3in ³

Table 4/4

Catalog Number	Volume, Box 2	Volume, Box 3
R34DM100		
R34DM10P1M5	42in ³	
R34DM200		
R34DV100		
R34DV200		
R34D00		
R34D0D1	42in ³	
R34D0P1	42in ³	
R44D4D0D1	30.3in ³	42in ³

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

