

nVent CADDY Heavy Duty Telescoping Bracket Between Stud Assembly



The nVent CADDY Heavy Duty Telescoping Bracket Between Stud Assembly line increases overall productivity, savings, and job site safety. For ultimate flexibility, the assemblies are configured with the most common box and mud ring combinations. The line is also offered in both standard and open back boxes as well as in single and double gang fixed or adjustable depth mud rings. When paired with the nVent CADDY Open Back Box, the assembly is ideal for prefab installations where devices, fittings, and cables are installed to quickly and easily complete make-up wiring connections, without the need to drop or work through the mud ring.

CERTIFICATIONS



FEATURES

Rigid and versatile - add/remove boxes quickly and easily

Prefab tab to prevent disassembly during transport, but allows for sliding on main bracket prior to final securement

Bracket will telescope and allow for easy positioning within wall stud

Box center plates slide to desired position prior to final securement

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/3

Catalog Number	Stud Spacing	Knockout Sizes, Box 1	Knockout Sizes, Box 2	Box Depth	Box Size 1	Box Size 2
TBP4DV2		(4) 1/2", 3/4", (8) 1/2"		2 1/8"	4"	

CatalogNumber	Stud Spacing	KnockoutSizes, Box 1	KnockoutSizes, Box 2	Box Depth	Box Size 1	Box Size 2
TBP4DM1	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"		2 1/8"	4"	
TBP4DM1PP1M 5	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"	(12) 1/2", 3/4"	2 1/8"	4"	4 11/16"
TBPX4M1	14 1/2" - 25"	(4) 1/2", 3/4", (7) 1/2"		2 1/8"	4"	
TBP4DM2		(4) 1/2", 3/4", (8) 1/2"		2 1/8"	4"	
TBP4DV1	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"		2 1/8"	4"	
TBPX4V1	14 1/2" - 25"	(4) 1/2", 3/4", (7) 1/2"		2 1/8"	4"	
TBP4D	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"		2 1/8"	4"	
TBP4DPD1	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"	(4) 1", (4) 1 1/4"	2 1/8"	4"	4 11/16"
TBP4DPP1	14 1/2" - 25"	(4) 1/2", 3/4", (8) 1/2"	(12) 1/2", 3/4"	2 1/8"	4"	4 11/16"
TBPX4	14 1/2" - 25"	(4) 1/2", 3/4", (7) 1/2"		2 1/8"	4"	

Table 2/3

Catalog Number	Box Type	Drywall Thickness	Gang, Box 1	Gang, Box 2	Ground Wire Included	Mud Ring Type
TBP4DV2	Closed	1/2" - 1 1/2"	2		Yes	Adjustable
TBP4DM1	Closed	5/8"	1		Yes	Raised
TBP4DM1PP1M 5		5/8"	1	1	Yes	Raised
TBPX4M1	Open	5/8"	1		Yes	Raised
TBP4DM2	Closed	5/8"	2		Yes	Raised
TBP4DV1	Closed	5/8" - 1 1/2"	1		Yes	Adjustable

CatalogNumber	Box Type	Drywall Thickness	Gang, Box 1	Gang, Box 2	Ground Wire Included	Mud Ring Type
TBPX4V1	Open	5/8" - 1 1/2"	1		Yes	Adjustable
TBP4D	Closed				Yes	
TBP4DPD1	Closed				Yes	
TBP4DPP1	Closed				Yes	
TBPX4	Open				Yes	

Table 3/3

Catalog Number	Volume, Box 1	Volume, Box 2
TBP4DV2	30.3in ³	
TBP4DM1	30.3in ³	
TBP4DM1PP1M5	30.3in ³	42in ³
TBPX4M1	32.8in ³	
TBP4DM2	30.3in ³	
TBP4DV1	30.3in ³	
TBPX4V1	32.8in ³	
TBP4D	30.3in ³	
TBP4DPD1	30.3in ³	42in ³
TBP4DPP1	30.3in ³	42in ³
TBPX4	32.8in ³	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

