

nVent CADDY Pyramid Crossover Bridge Turn Kit



FEATURES

Turn bridges allow for configurations beyond a straight pathway, "L", "U" or "Z" pathways can be created by using turn bridges

Interchangeable components are easily assembled yielding labor-saving and quick installations

nVent CADDY Pyramid bases provide superior load distribution and roof membrane compatibility

Foam bottom offers low abrasion interface for better roof membrane protection

Aluminum construction designed to withstand harsh environments

Walking surfaces with serrated tread provides maximum slip resistance and drainage

Compliant with OSHA, Cal/OSHA and ANSI® standards

SPECIFICATIONS

Material: Aluminum;Polypropylene;Polyethylene

Table 1/1


Catalog Number	Walkway Height	Height (H)	Width (W)	Depth (D)	Static Load (F)
PCB36H20	20"	62"	52 1/2"	47.1"	500lb
PCB36H30	30"	72"	52 1/2"	47.1"	500lb
PCB36H40	40"	82"	52 1/2"	47.1"	500lb

Catalog Number	Walkway Height	Height (H)	Width (W)	Depth (D)	Static Load (F)
PCB36H50	50"	92"	52 1/2"	47.1"	500lb
PCB36H60	60"	102"	52 1/2"	47.1"	500lb

ADDITIONAL PRODUCT DETAILS

Clearance of walkway is 3" less than the walkway height.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

