

nVent CADDY Pyramid Crossover Ladder, 90°



FEATURES

Vertical ladders ideal for tight spaces

Interchangeable components are easily assembled yielding labor-saving and quick installations

nVent CADDY Pyramid bases provide superior load distribution and roof membrane compatibility

Foam bottom offers low abrasion interface for better roof membrane protection

Aluminum construction designed to withstand harsh environments

Walking surfaces with serrated tread provides maximum slip resistance and drainage

Compliant with OSHA, Cal/OSHA and ANSI® standards

SPECIFICATIONS

Material: Aluminum;Polypropylene;Polyethylene

Table 1/2

Catalog Number	Walkway Height	Number of Steps	Height (H)	Width (W)	Depth (D)	A
PCL90S2	20"	2	62"	52.4"	29.2"	12"
PCL90S3	30"	3	72"	52.4"	29.2"	12"
PCL90S4	40"	4	82"	52.4"	29.2"	12"
PCL90S5	50"	4	92"	52.4"	29.2"	12"


CatalogNumber	WalkwayHeight	Number of Steps	Height (H)	Width (W)	Depth (D)	A
PCL90S6	60"	5	102"	52.4"	29.2"	12"

Table 2/2	
Catalog Number	Static Load (F)
PCL90S2	500lbf
PCL90S3	500lbf
PCL90S4	500lbf
PCL90S5	500lbf
PCL90S6	500lbf

ADDITIONAL PRODUCT DETAILS

Clearance of walkway is 3" less than the walkway height.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

