

nVent CADDY Pyramid Equipment Support Kit, 6 Post Base



CERTIFICATIONS



FEATURES

Kit includes post-base assemblies, frame and equipment-support clamps

Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated

SPECIFICATIONS

Table 1/3

Catalog Number	Material	Finish	Temperature	Height (H)	Length (L)	Post Base (A)
PEK6B	Steel, Polypropylene, Polyethylene	Hot-Dip Galvanized	-30 to 130 °F	12" - 18"	85 1/2"	12" x 6 pc

Table 2/3

Catalog Number	Square Tube (B)	Cross Bar Assembly (C)	Width (W)	Surface Area	Unit Weight	Ultimate Static Load (F)
PEK6B	78" x 2 pc	48.5" x 4 pc	62 1/2"	862in ²	123 lb	2240lb


Table 3/3

Catalog Number	Static Load Safety Factor
PEK6B	3:1

ADDITIONAL PRODUCT DETAILS

Static load must be stable and uniformly distributed across frame.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

