

nVent CADDY Pyramid RL Fixed Roller Support



CERTIFICATIONS



FEATURES

Roller-based support designed specifically for rooftop applications

Roller capability allows longitudinal movement of pipe, resulting from thermal expansion or contraction

Polymeric rollers ensure corrosion free rotation

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Ready to use out of the box, saving installation time and labor

Hot-dip galvanized and UV stabilized for long lasting performance

SPECIFICATIONS

Static Load Safety Factor:	3:1
Finish:	Hot-Dip Galvanized
Material:	Polyethylene;Polypropylene;Steel
Temperature:	-50 to 150 °F


Table 1/2

Catalog Number	Pipe Size	Height (H)	Length (L)	Width (W)	A	Surface Area
----------------	-----------	------------	------------	-----------	---	--------------

PRF2	2" Max	5.8"	8"	6"	4 1/2"	41in ²
PRF3	3" Max	6 1/4"	12 1/2"	8"	6 1/4"	92in ²
PRF6	6" Max	6 1/4"	19"	8"	10 1/4"	142in ²

Table 2/2			
Catalog Number	Unit Weight	Static Load (F)	Certifications
PRF2	1 lb	100lbf	ITB
PRF3	2 lb	250lbf	
PRF6	3 lb	600lbf	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

