

nVent CADDY Pyramid Tool-Free Pipe Clamp



FEATURES

Push-in clamps install without the need for additional tools or strut clamps

Clamps come in two different sizes to fit project needs

Plastic clamps and base will not corrode pipe

SPECIFICATIONS

Temperature: -50 to 150 °F

Material: Nylon

Table 1/1

Catalog Number	Outer Diameter (OD)	Length (L)	Width (W)	A	Unit Weight
PTF1C	1/2" - 1.32"	1.6"	3/4"	3/8"	0.03 lb
PTF2C	0.840" - 2.38"	3.2"	3/4"	3/8"	0.04 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

